PHILIPS

PocketMemo

Voice Recorder

Digita

Slide-switch operation

Two microphones

SpeechExec software



DPM7000 series



First-class recording

with outstanding ergonomics

The PocketMemo digital Voice Recorder takes dictation to a new level. Two microphones deliver superior audio quality for your dictations. Its robust yet lightweight stainless steel design offers perfect ergonomics for working over longer periods of time. The classic mode gives the user the look and feel of working with an analog device, allowing you to focus on the essentials while retaining the advantages of digital technology.

Superior audio quality and design

- · Two microphones for superior stereo audio recordings
- Wear-free ergonomic slide switch for efficient single-handed operation
- · Robust stainless steel casing for extra durability

Enhance your productivity

- · SpeechExec dictation software for efficient data management
- · Large color display and intuitive user interface for easy, convenient operation
- · Power saving measures and Li-ion battery for extended use

Designed for professionals

- $\boldsymbol{\cdot}$ Priority setting for getting urgent jobs processed first
- · High recording quality in DSS and MP3 format
- · Classic mode for clear and easy-to-use operation
- Optional docking station and foot pedal for hands-free dictation and transcription even without a computer



Highlights

Superior audio quality



The built-in microphones deliver superior stereo audio recordings. The crystal clear recordings are perfectly suitable for speech recognition.

Wear-free slide switch



The quick-response and ergonomic slide switch is designed for single-handed operation of all recording and playback functions, allowing easy and quick file editing (insert, overwrite, append). It operates with a light sensor signal, making it wear-free and durable.

Robust and ergonomic design



The asymmetrical and ergonomic shape fits perfectly into your hand. Its slim and lightweight design maximizes comfort, even when working over longer periods of time. The stainless steel creates a robust and highly durable protective shell around the device. The device is shockproof according to US military standard 516.6.

SpeechExec workflow software



The SpeechExec Dictate software organizes the workflow of dictation files and resulting documents between author and transcriptionist, and allows you to monitor the status of your work.

Large color display



The large full-color display offers sharp images, making it easier to see everything at first glance. The clear user interface is optimized for easy, intuitive operation.

Extended battery life



The high-capacity Li-ion battery can be easily charged through a standard micro USB jack. The integrated light sensor guarantees extended battery life, up to 50% longer than competition. The smart technology adjusts the brightness of the display, ensuring that your recorder will always be ready to work when you are.

Priority settings



With the included priority setting option, urgent recordings can be processed first. This makes sure important recordings are not overseen and helps you and your transcriptionists manage your workloads better

DSS and MP3 recording



The DSS format was developed for the use in digital voice recorders, achieving a high compression ratio with little loss of quality. The DSS format also allows you to store additional information in the file header, which facilitates the organization and the transcription of dictation files. The MP3 format is the common audio format for consumer audio storage, as well as a de facto standard encoding for the transfer and playback on digital audio players.











Highlights

Classic mode



Many users still love their analog devices for their simplicity and user-friendliness. The optional classic mode gives the user the look and feel of working with an analog device while retaining the advantages of digital technology and keep focused on the essentials.

Optional docking station



The stable and practical Docking Station provides speedy charging and automatic transfer of your recordings to your computer. With the optional foot pedal connected, the docking station even enables handsfree recording and transcription without a computer.

Versions

DPM7000



4-position slide switch (record, stop, play, fast rewind)

SpeechExec Basic Dictation Software (2-year subscription included)

DPM7200



Configurable 4-position slide switch (fast forward, play/record, stop, fast rewind), SpeechExec Basic Dictation Software (2-year subscription included)











Specifications

Connectivity

Headphones: 3.5 mm Microphone: 3.5 mm USB: micro USB 2.0 Docking connector Memory card slot

Display

Type: color TFT

Diagonal screen size: 2.4 inches / 6.1 cm Resolution: 320 × 240 pixels

Storage media

Exchangeable memory card

Memory card types: SD/SDHC, up to 32 GB

Mass storage class compliant

Data transfer speed: 6.75 MB/s read speed,

5.0 MB/s write speed

Audio recording

Recording format: DSS (Digital Speech

Standard), MP3, PCM

Built-in microphones: 2 omnidirectional microphones for stereo recording

Recording modes: DSS QP (.ds2/mono), DSS SP (.dss/mono), MP3 (.mp3/stereo), PCM Voice (.wav/mono), PCM Stereo (.wav/stereo) Bit rate: 13.7 kbit/s (DSS SP), 28 kbit/s (DSS QP), 192 kbit/s (MP3), 353 kbit/s (PCM Voice), 705 kbit/s (PCM Stereo)

Edit modes: insert (DSS), overwrite (DSS, MP3, PCM), append (DSS, MP3, PCM)
Recording time (4 GB memory card): 700

hours (SP), 350 hours (QP), 50 hours (MP3), 27 hours (PCM Voice), 13 hours (PCM Stereo)
Sample rate: 44.1 kHz (MP3), 22.05 kHz (PCM), 16 kHz (DSS QP), 12 kHz (DSS SP)

Sound

Speaker type: built-in round, dynamic

speaker

Speaker diameter: 28 mm

Acoustic frequency response: 300 – 7500 Hz

Speaker output power: > 200 mW

Power

Battery type: Philips Rechargeable Li-ion

Battery ACC8100

Battery capacity: 1000mAh

Battery lifetime: up to 30 hours of recording

(DSS mode)

Standby time: more than 200 days Charging time (full charge): 3 hours

System requirements for Philips SpeechExec software

Processor: Intel dual core or equivalent AMD processor, 1 GHz or faster processor

RAM: 4 GB (64 bit)

Hard-disk space: 100 MB for SpeechExec software, 4.5 GB for Microsoft .NET

Framework

Operating system: Windows 11 Pro, Windows

10 Pro/Enterprise (64 bit)

Graphics: DirectX-compliant graphics card with hardware acceleration recommended Sound: Windows-compatible sound device

Free USB port Internet connection

Green specifications

Compliant to 2011/65/EU (RoHS) Lead-free soldered product

Operation conditions

Temperature: $-5^{\circ} - 45^{\circ}$ C/23° $- 113^{\circ}$ F Humidity: 10 % - 90 %, noncondensing

Dimensions

Product dimensions (W×D×H): 53×123×15 mm/2.1×4.8×0.6 inches Weight: 117 g/4.1 oz including battery and memory card

Package contents

PocketMemo Voice Recorder

Memory card

Rechargeable attery

USB cable

Pouch

SpeechExec Basic Dictation Software (2-year

subscription included) Quick start guide **Available accessories**

Philips Rechargeable Li-ion Battery ACC8100 Philips SDHC Memory Card ACC9008

LFH9162

Philips Meeting Microphone LFH9172 Philips Docking Station ACC8120 Philips Foot Pedal LFH2210

Philips Telephone Pickup Microphone

© 2022 Speech Processing Solutions GmbH. All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.



Issue date 2022-01-04

Version 1.0