

PHILIPS

PocketMemo

Voice Recorder

Digital

Push-button operation

Two microphones

SpeechExec software



DPM6000



First-class recording

with outstanding ergonomics

The PocketMemo Voice Recorder takes dictation to a new level. Two microphones deliver superior audio quality for your dictations. Its robust yet lightweight stainless steel design offers perfect ergonomics for working over longer periods of time. Power saving features and a high capacity Li-ion battery offer extended recording time and easy charging through a standard USB connection.

Superior audio quality and design

- Two microphones for superior stereo audio recordings
- Convenient push-button for professional recording control
- Robust stainless steel casing for extra durability

Enhance your productivity

- SpeechExec workflow software for efficient data management
- Large color display and intuitive user interface for easy, convenient operation
- Light sensor and Li-ion battery for extended use

Designed for professionals

- Priority setting for getting urgent jobs processed first
- High recording quality in DSS and MP3 format
- Optional docking station and foot pedal for hands-free dictation and transcription even without a computer



No 1 in SPS global customer satisfaction survey 09/2015.

Highlights

Superior audio quality



The built-in microphones deliver superior stereo audio recordings. The crystal clear recordings are perfectly suitable for speech recognition.

Professional recording control



The recorder is designed for single-handed operation of all recording and playback functions, allowing easy and quick file editing (insert, overwrite, append) via convenient push-button operation.

Robust and ergonomic design



The asymmetrical and ergonomic shape fits perfectly into your hand. Its slim and lightweight design maximizes comfort, even when working over longer periods of time. The stainless steel creates a robust and highly durable protective shell around the device. The device is shockproof according to US military standard 516.6.

SpeechExec workflow software



The SpeechExec Dictate software organizes the workflow of dictation files and resulting documents between author and transcriptionist, and allows you to monitor the status of your work.

Large color display



The large full-color display offers sharp images, making it easier to see everything at first glance. The clear user interface is optimized for easy, intuitive operation.

Extended battery life



The high-capacity Li-ion battery can be easily charged through a standard micro USB jack. The integrated light sensor guarantees extended battery life, up to 50% longer than competition. The smart technology adjusts the brightness of the display, ensuring that your recorder will always be ready to work when you are.

Priority settings



With the included priority setting option, urgent recordings can be processed first. This makes sure important recordings are not overseen and helps you and your transcriptionists manage your workloads better.

DSS and MP3 recording



The DSS format was developed for the use in digital voice recorders, achieving a high compression ratio with little loss of quality. The DSS format also allows you to store additional information in the file header, which facilitates the organization and the transcription of dictation files. The MP3 format is the common audio format for consumer audio storage, as well as a de facto standard encoding for the transfer and playback on digital audio players.

Optional docking station



The stable and practical Docking Station provides speedy charging and automatic transfer of your recordings to your computer. With the optional foot pedal connected, the docking station even enables hands-free recording and transcription without a computer.

Specifications

Connectivity

Headphones: 3.5 mm
 Microphone: 3.5 mm
 USB: micro USB 2.0
 Docking connector
 Memory card slot

Display

Type: color TFT
 Diagonal screen size: 2.4 inches / 6.1 cm
 Resolution: 320 × 240 pixels

Storage media

Exchangeable memory card
 Memory card types: SD/SDHC, up to 32 GB
 Mass storage class compliant
 Data transfer speed: 6.75 MB/s read speed,
 5.0 MB/s write speed

Audio recording

Recording format: DSS (Digital Speech Standard), MP3, PCM
 Built-in microphones: 2 omnidirectional microphones for stereo recording
 Recording modes: DSS QP (.ds2/mono), DSS SP (.dss/mono), MP3 (.mp3/stereo), PCM Voice (.wav/mono), PCM Stereo (.wav/stereo)
 Bit rate: 13.7 kbit/s (DSS SP), 28 kbit/s (DSS QP), 192 kbit/s (MP3), 353 kbit/s (PCM Voice), 705 kbit/s (PCM Stereo)
 Edit modes: insert (DSS), overwrite (DSS, MP3, PCM), append (DSS, MP3, PCM)
 Recording time (4 GB memory card): 700 hours (SP), 350 hours (QP), 50 hours (MP3), 27 hours (PCM Voice), 13 hours (PCM Stereo)
 Sample rate: 44.1 kHz (MP3), 22.05 kHz (PCM), 16 kHz (DSS QP), 12 kHz (DSS SP)

Sound

Speaker type: built-in round, dynamic speaker
 Speaker diameter: 28 mm
 Acoustic frequency response: 300 – 7500 Hz
 Speaker output power: > 200 mW

Power

Battery type: Philips rechargeable Li-ion battery ACC8100
 Battery capacity: 1000mAh
 Battery lifetime: up to 30 hours of recording (DSS mode)
 Standby time: more than 200 days
 Charging time (full charge): 3 hours

System requirements for Philips SpeechExec software

Processor: Intel dual core or equivalent AMD processor, 1 GHz or faster processor
 RAM: 4 GB (64 bit)
 Hard-disk space: 100 MB for SpeechExec software, 4.5 GB for Microsoft .NET Framework
 Operating system: Windows 10 Pro/Enterprise (64 bit)
 Graphics: DirectX-compliant graphics card with hardware acceleration recommended
 Sound: Windows-compatible sound device
 Browser: Internet Explorer 9 or higher, or the current version of Chrome or Firefox
 Free USB port
 Internet connection

Green specifications

Compliant to 2011/65/EU (RoHS)
 Lead-free soldered product

Operation conditions

Temperature: -5° – 45° C/23° – 113° F
 Humidity: 10 % – 90 %, noncondensing

Dimensions

Product dimensions (W×D×H):
 53×123×15 mm / 2.1×4.8×0.6 inches
 Weight: 117 g/4.1 oz including battery and memory card

Package contents

PocketMemo digital Voice Recorder
 Memory card
 Rechargeable battery
 USB cable
 Pouch
 SpeechExec Basic Dictation Software (2-year subscription included)
 Quick start guide

Available accessories

Philips Rechargeable Li-ion Battery ACC8100
 Philips SDHC Memory Card ACC9008
 Philips Telephone Pickup Microphone LFH9162
 Philips Meeting Microphone LFH9172
 Philips Docking Station ACC8120
 Philips Foot Pedal LFH2210

