# **PHILIPS**

### **Voice**Tracer

### Audio recorder

Digital

Notes recording

8 GB

PC connection



DVT1250



# Easy notes recording

### with 8 GB audio recording

The VoiceTracer 1250 is the perfect voice recorder for capturing notes, ideas and thoughts on the go. Thanks to the micro SD memory card slot you can easily expand your memory up to 32 GB.

#### **Superior voice recording**

· Voice activation function for hands-free recording

#### Easy and intuitive experience

- PC connection for plug & play
- · Backlight display for easy file navigation

#### Designed around you

- · 8 GB built in for extra long recording hours
- MicroSD memory card slot for virtually unlimited recording
- Extra long battery runtime for longer recording sessions



# Highlights

#### **Voice-activation function**



Voice-activated recording is a convenience feature for hands-free recording. When enabled, recording will start automatically when you start speaking. Recording stop automatically after you stop speaking and restart automatically when you start speaking again.

#### Plug and play



Just plug your recorder into your PC and play in Windows and macOS.

### Large backlit display



The large graphical display lets you view all important file information at a glance, even in poor lighting conditions, thanks to the backlit display.

#### 8 GB memory built-in



With the 8 GB of built-in memory, your recorder is able to capture multiple days of continuous recording.

#### Micro SD memory card slot



Virtually unlimited recording capacity thanks to a micro SD memory card slot supporting up to 32 GB of additional memory.

#### Extra long battery runtime



The batteries of the new recorder last for up to 42 hours for extra long recording sessions.

## Specifications

#### Connectivity

Headphones: 3.5 mm

Line-in

USB: High-speed USB 2.0

#### Display

Type: Dot matrix LCD
Resolution: 112 × 112 pixels
Diagonal screen size: 33 mm

Multi language: English, French, German,

Spanish, Italian, Russian, Polish

#### Storage media

Built-in memory capacity: 8 GB Built-in memory type: NAND Flash

USB mass storage

SD card support: up to 32 GB

#### **Audio recording**

Built-in microphone: 1 channel

Recording formats: WAV (ADPCM and PCM) Recording modes: HQ (PCM), SP (PCM), LP

(ADPCM)

Sample rate: 24 kHz (PCM/SHQ), 8 kHz (HQ), 8

kHz (SP/LP)

Bit rate: 384kbps (PCM), 128kbps (PCM), 32

kbps (ADPCM)

Recording time (internal memory): 48 h (HQ mode), 146 h (SP mode), 583 h (LP mode)

#### Sound

Frequency response: 750Hz – 18KHz

Speaker type: round Speaker diameter: 28 mm

#### Convenience

Instant one-touch recording Voice-activated recording

Keypad lock

Firmware upgradeable Variable playback speed

Optimized for notes

Microphone sensitivity: high/low

Timed recording

Line-in

Real-time clock

Remaining time display

Noise reduction

File lock

Index (up to 10)

All rights reserved.

A-B repeat

#### Power

Battery lifetime: up to 42 hours Battery type: 2 × AAA battery Number of batteries: 2 Batteries included: yes

#### **System requirements**

Free USB port

Operating system: Windows 10/8/7, macOS 10

#### **Product dimensions**

Product dimensions (W  $\times$  H  $\times$  D):

108 × 37 × 19 mm Weight: 67 g

#### **Design and finishing**

Color(s): Dark silver & black

#### **Package contents**

Quick start guide

VoiceTracer audio recorder 2 × AAA batteries USB cable

© 2017 Speech Processing Solutions GmbH.

Specifications are subject to change without notice. Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. and are used by Speech Processing Solutions GmbH under license from Koninklijke Philips N.V. All trademarks are the property of their respective owners.



Issue date 2017-08-17

Version 1.0