PHILIPS

VoiceTracer

Audio Recorder

with Sembly Speech-to-Text Cloud Software

High-quality microphones

40 hours battery runtime

8 GB and memory card slot

Automatic speech-to-text



DVT2015



Exceptional recording, automatic speech-to-text

The perfect audio recorder for easily capturing voice recordings including notes, interviews, and small meeting settings. Thanks to its excellent sound quality, long-lasting battery and large extendable memory, it is the ideal alternative to recording with your smartphone. Combined with Sembly's AI Speech-to-Text Cloud Software, you can even turn your recordings into text quickly and accurately. Simply upload your files to Sembly when you are back at your computer and let it automatically convert your recordings to text for you.

Superior audio quality

- · Two high-quality stereo microphones for excellent sound quality
- · Stereo MP3 and PCM recording for clear playback and easy file sharing
- 8 GB internal memory storage for extra-long recording hours

Designed for ease-of-use

- · No installation required for quick plug & play
- ${}\cdot{}$ Backlight display for easy file navigation in low-light situations
- · Micro SD memory card slot for virtually unlimited recording

Turn your speech into text with Sembly

- Automatically convert your recordings to text, up to three times faster than typing
- · Automatic meeting minutes with multi-speaker transcription for easy following up
- Easily share your voice or meeting recordings with colleagues, family or classmates





Highlights

High-quality stereo microphones



The two high-quality stereo microphones deliver crystal-clear sound quality when recording notes, ideas and thoughts on the go.

MP3 and PCM recording



Capture your recordings in stereo MP3 or PCM format. The popular file formats allows you to play back your files virtually anywhere and simply share them with others. The PCM (WAV) format allows stereo recording of lossless, uncompressed sound in studio-like audio quality.

8 GB memory built-in



With the 8 GB of built-in memory, your recorder is able to capture multiple days of continuous recording.

Plug and play



The recorder requires no special installation. Simply plug your recorder into your PC or Mac and play back your files or transfer them to your computer right away.

Large backlit display



The large backlit display allows you to see all important file information clearly at a glance. This makes file navigation easier, even in low-light situations.

Micro SD memory card slot



Virtually unlimited recording capacity thanks to a micro SD memory card slot supporting up to 32 GB of additional memory.

Automatic speech-to-text



Put an end to tedious typing and create text documents directly from recorded audio files. Using the Sembly Speech-to-Text Cloud Software is at least three times quicker than typing up the document yourself. Simply record your notes, interviews or meetings, upload them to Sembly, and receive a written document almost instantly.

Automatic meeting minutes



If you want to record meetings, Sembly Speech-to-Text Cloud Software creates automatic meeting minutes, so you can focus on your conversation and not get distracted by having to take notes. Thanks to multispeaker identification you can clearly identify who said what.

Easy sharing



Sembly allows to save transcriptions on your computer in PDF or markdown format. You can easily share your voice recordings and transcripts with colleagues, family or classmates by simply sending them a link. For increased privacy, you can add a password to your link.



Specifications

Connectivity

Headphones: 3.5 mm, impedance 16 Ohm or

more Line-in

USB: high-speed USB 2.0

Display

Type: dot matrix LCD Resolution: 112 × 112 pixels Diagonal screen size: 33 mm

Multi language: English, French, German,

Spanish, Italian, Russian

Storage media

Built-in memory capacity: 8 GB Built-in memory type: NAND Flash

USB mass storage

Micro-SD card socket: up to 32 GB

Audio recording

Built-in microphone: stereo

Recording formats: WAV (PCM), MP3

Recording modes: PCM (WAV), HQ (MP3), SP

(MP3), SLP (MP3)

Sample rate: 48k, 32k, 16k, 8k

Bit rate: 1536kbps (WAV), 192kbps (MP3),

64kbps (MP3), 8kbps (MP3)

Recording time (built-in memory): 12 h (PCM

mode), 90 h (HQ mode), 297 h (SP mode),

2370 h (SLP mode)

Microphone sensitivity: high / low

Recording timer

Instant one-touch recording

Voice-activated recording FM Recording

Sound

Speaker type: round
Speaker diameter: 28 mm

Music playback

MP3 playback

Supported bitrate: 8 to 320 kbps

Tuner

Auto digital tuning Tuner bands: FM stereo

Frequency range: 87.5 - 108 MHz

© 2023 Speech Processing Solutions GmbH. All rights reserved.

Specifications are subject to change without notice. Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. and are used under license. All trademarks are the property of their respective owners.

Convenience

Keypad lock

Firmware upgradeable

Variable playback speed

Real-time clock

Noise reduction

File lock

Index (up to 10)

A-B repeat

Power

Battery type: 2 × AAA

Battery lifetime: up to 40 hours of recording

System requirements

Free USB port

Operating system: Windows, macOS

Design and finishing

Color(s): aluminium light silver metal front and black

Sembly Speech-to-Text Cloud Software

Works with any web browser under Windows

and macOS

iOS and Android Sembly app available

Internet connection required

 $Sembly\ Personal\ Plan\ voucher\ included:$

1 hour of audio upload per month + voucher

for additional 15 hours

Sembly transcription languages: English, French, Spanish, German, Italian, Portuguese,

Dutch, Japanese (+28 more)

Package contents

Recorder

Headphones

2 AAA batteries

USB cable

Quick start guide

Sembly voucher

Product dimensions

Product dimensions (W \times H \times D):

111 × 38 × 19 mm Weight: 55 g/1.9 oz GTIN-12: 855971 006878

GTIN-13: 0 855971 006878



Issue date 2023-07-19

Version 1.0

www.philips.com/dictation