

PHILIPS

DVT2075

Philips VoiceTracer Audio Recorder

- High-quality microphones
- Stereo MP3 and PCM recording
- 35 hours battery runtime
- 8 GB and memory card slot

Professional recording made simple

with rich stereo sound

The Philips VoiceTracer DVT2075 is engineered for recording interviews, meetings, and conversations with superior clarity. Featuring high-grade stereo microphones, multiple recording formats, extended battery life, and expandable storage, it's the smart choice for users who expect more than a smartphone can offer. Combined with Sembly's AI Notes software, you can even turn your recordings into text quickly and accurately.



Includes
Sembly AI Notes
software trial



Premium stereo audio

- Dual high-sensitivity microphones for natural stereo sound
- Supports MP3 and PCM formats for easy sharing or lossless recording
- Audio scenes presets optimize audio settings in any recording situation

Intuitive experience

- Voice-activation recording for hands-free use
- Time-stamped files for easy organization and navigation
- One-touch operation to start recording instantly

Ready when you are

- 8 GB of internal memory and microSD card slot for expanded capacity
- Rechargeable battery provides up to 35 hours of recording time
- Sembly AI Notes software turns your recordings into transcripts and summaries


Highlights

High-quality stereo microphones



Two built-in microphones capture a true stereo field, delivering clean, accurate sound even in dynamic environments.

Voice-activation function



Enjoy hands-free convenience: recording starts when you speak and stops when you're silent—ideal for dictation and meetings.

Rechargeable long-life battery



Built-in Li-ion polymer battery lasts up to 35 hours and fully recharges in just 2 hours via USB-C.

MP3 and PCM recording




Record your audio in stereo using either MP3 or PCM formats. MP3 offers wide compatibility and is ideal for quick playback and easy sharing across devices. For maximum audio fidelity, PCM (WAV) provides uncompressed, lossless stereo recording in CD-quality sound.

Time-stamped recording




Easily navigate through your files with embedded date and time stamps, helping you locate specific recordings quickly.

Sembly AI Notes trial



With Sembly AI Notes software, creating written documents is up to three times faster than typing them yourself. Just record your notes, interviews, or meetings, upload the audio to Sembly, and receive an accurate transcript within moments—complete with high-quality summaries and key insights automatically extracted.

Audio scenes



Optimize recording quality with predefined scenes for memos, meetings, or music. Each scene adjusts the audio settings automatically to suit your environment. A dedicated Personal scene also lets you customize file format settings to match your specific recording needs.

One-touch recording



Just press and hold the record button to turn the device on and begin recording immediately.

8 GB memory and microSD card slot



Record for days with 8 GB of internal memory, ensuring you never miss important content due to lack of space. Expand storage capacity by inserting a microSD card, enabling virtually unlimited recording time.

Specifications

Connectivity

Headphones: 3.5 mm
Microphone: 3.5 mm, stereo socket
USB: type C, high-speed USB 2.0

Display

Type: LCD color display
Backlight
Diagonal screen size: 36 mm / 1.44 in
Resolution: 128 x 128 pixels

Storage media

Built-in memory capacity: 8 GB
Built-in memory type: NAND Flash
USB mass storage
MicroSD card socket: up to 128 GB

Audio recording

Built-in microphone: 2 channel stereo
Recording formats: MPEG1 layer 3 (MP3), PCM (WAV)
Recording quality: MP3 (64, 128, 192 kbps), PCM (1536 kbps, 48 kHz/16 bit)
Audio scenes: Memo, Meeting, Music, Personal
Recording time (built-in memory): 270 h (MP3, 64 kbps), 135 h (MP3, 128 kbps), 90 h (MP3, 192 kbps) 11 h (PCM)
Auto-divide function: 30, 60 minutes
Bookmark function: up to 10 per file
Voice-activated recording
Instant one-touch recording
Record monitor function
Recording timer

Sound

Frequency response: 200 Hz – 20 kHz
Speaker type: oval
Speaker size: 20 x 30 mm
Speaker output power: 1 W

Convenience

Instant one-touch recording
Voice-activated recording
Keypad lock
Variable playback speed
Real-time clock
Remaining time display
Bookmarks (up to 10 per file)
File repeat
A-B repeat

Power

Battery type: built-in rechargeable Li-ion polymer battery
Battery capacity: 700 mAh
Battery lifetime: up to 35 hours of recording (MP3, 64 kbps)
Rechargeable: yes
Charging time (full charge): 2 hours

System requirements

Free USB port
Operating system: Windows, macOS

Product dimensions

Product dimensions (W x H x D): 115 x 39.5 x 15 mm/4.5 x 1.6 x 0.6 mm
Weight: 51 g/1.8 oz
GTIN-12/13: (0)855971006984

Design and finishing

Color(s): metallic graphite gray, matte black, silver

Sembly AI Notes software

Register for a free 30-day trial and get 30 hours of audio upload + 1 hour of audio upload per month on top of the monthly upload limit in your selected Sembly plan in the first year. Credit card required for sign-up. Not charged until the free trial is over. Works with any web browser under Windows and macOS
Internet connection required
Sembly transcription languages: English, French, Spanish, German, Italian, Portuguese, Dutch, Japanese (+ 30 more)

Package contents

Recorder
Quick start guide
USB-C cable
Sembly voucher

Operation conditions

Temperature: 5° – 45° C/41° – 113° F
Humidity: 10 % – 90 %, non-condensing

