

PHILIPS

VoiceTracer

Audio Recorder

Dragon speech recognition software

Notes recording

8 GB

PC connection



DVT2710



Turn your voice into text

with first-class recordings and speech recognition

Record documents and notes on the move in high quality. Back at your desk, simply connect the recorder to your computer, transfer your files and let the included software automatically turn your speech into text.

Superior audio quality

- 2Mic stereo recording for outstanding audio quality
- MP3 recording for clear playback and easy file sharing
- Voice-activation for hands-free recording

Turn your voice into text

- Dragon speech recognition software included
- Automatically transcribe your dictation files
- Exceptional transcription accuracy rate of up to 99 %

Designed around you

- Large color display for easy and intuitive operation
- 8 GB memory built-in for up to 88 days of recording
- MicroSD memory card slot for virtually unlimited recording



Highlights

2Mic stereo recording



The two built-in stereo microphones are designed to deliver clear voice recordings and reduce background noise, even in noisy environments. High-quality recording is essential for clear playback and accurate speech recognition results.

Speech recognition software



Put an end to tedious typing and create text documents directly from recorded audio files. Dragon NaturallySpeaking speech recognition software automatically converts your recording into a text file.

Large color display



The large color display offers sharp images, making it easier to see and read everything at first glance. The clear user interface supports eight languages and is optimized for easy, intuitive operation.

MP3 recording



Capture your recordings in MP3. The popular file format allows you to play back your files virtually anywhere and simply share them with others.

Automatic transcription



Simply record your documents and notes, connect the recorder to the computer, click the 'Transcribe' button and Dragon NaturallySpeaking speech recognition software does the transcription work for you.

8 GB internal memory



Capture and store up to 88 days of continuous recording thanks to the 8 GB of internal memory.

Voice-activated recording



Voice-activated recording is a convenient feature for hands-free recording. When enabled, recording will start automatically when you begin speaking. Recording pauses when you stop and resumes automatically when you begin speaking again.

Exceptional accuracy



Dragon NaturallySpeaking speech recognition software provides an astounding accuracy rate of up to 99 % and accuracy continues to increase the more you use the software. Dragon also never misspells a word, so typos are a thing of the past.

MicroSD memory card slot



Virtually unlimited recording and storage capacity thanks to a microSD memory card slot supporting up to 32 GB of additional memory.

Specifications

Connectivity

Headphones: 3.5 mm
Micro-SD card socket
USB: High-speed USB 2.0

Display

Type: LCD color display
Backlight
Diagonal screen size: 1.77"/4.5 cm
Resolution: 128 × 160 pixels

Audio recording

Built-in microphone: HQ Stereo, low-noise microphone
Recording formats: MPEG1 layer 3 (MP3), PCM (WAV)
Recording modes: PCM 1411 kbps, SHQ 192 kbps, HQ 96 kbps, SP 64 kbps, LP 8 kbps
Sample rate: 44,1 kHz (PCM/SHQ), 32 kHz (HQ), 22 kHz (SP), 16 kHz (LP)
Bit rate: 8, 64, 96, 192, 1411 kbps
File overwrite and append mode
Record monitor function
Recording time: 2280 h (LP), 284 h (SP), 190 h (HQ), 90 h (SHQ), 12 h (PCM)
Silent recording mode
Prerecording mode

Sound

Sound enhancement: ClearVoice
Frequency response: 50–20,000 Hz
Signal-to-noise ratio: > 60 dB
Speaker output power: 110 mW
Speaker diameter: 28 mm

Storage media

Built-in memory capacity: 8 GB
Built-in memory type: NAND Flash
Mass storage class compliant

Convenience

Firmware upgradeable
Keypad lock
Multi language: English, French, German, Spanish, Italian, Russian, Polish, Simplified Chinese (menu languages of the VoiceTracer)
Variable playback speed
Voice volume indicator
Voice-activated recording
Calendar search
Instant one-touch recording
Optimized for notes

Power

Batteries included
Battery lifetime: up to 50/25 hours in LP record mode (built-in memory / microSD memory card)
Battery type: AAA/LR03 Alkaline
Number of batteries: 2
Rechargeable: no

System requirements (software)

Operating system: Windows 10, 8.1, 8, 7 Service Pack 1 (32/64 bit), Windows Server 2008 R2 Service Pack 1 (64 bit), Windows Server 2012
Processor: Intel dual core or equivalent AMD, 2.2 GHz or later (SSE2 instruction set required), L2 Cache: 512 KB
RAM memory: 2 GB (32 bit)/4 GB (64 bit)
Hard disk space: 4 GB
Sound card: capable of supporting 22 kHz 16-bit recording
DVD-ROM drive
USB: free USB port

Green specifications

Lead-free soldered product

Design and finishing

Color(s): Anthracite/chrome

Package contents

Recorder
DVD-Rom with Speech Recognition software
USB cable
2 × AAA batteries
Quick start guide

Product dimensions

Product dimensions (W × H × D):
4.5 × 11.3 × 2.0 cm / 1.77 × 4.45 × 0.79 inch
Weight: 79 g/2.79 oz.
EAN: 0855971006182

