PHILIPS

VoiceTracer

Audio Recorder

For lectures and interviews

3 high-fidelity microphones

Remote control & sharing app

8 GB and memory card slot

Long-lasting battery



DVT4110



Exceptional recording, shared instantly

Capture lectures and distant speakers in outstanding sound quality thanks to the three specialized high-fidelity microphones. Record and control your recorder remotely using your smartphone app for even greater flexibility. Easily share your files with the world via the app.

Superior audio quality

- Three specialized stereo microphones for capturing distant speakers
- · Stereo MP3 and PCM recording for clear playback and easy file sharing
- · 8 GB internal memory for up to 88 days of recording
- · Rechargeable Li-ion polymer battery for extra-long recording

Easy and intuitive experience

- · Free smartphone app for remote audio control
- Smartphone app for easy sharing of recordings
- · Large color display for clear recording status information
- $\boldsymbol{\cdot}$ $\,$ Audio scences for automatic perfect audio settings in any situation

Designed around you

- · Plug and play in Windows, macOS and Linux
- · Tripod mount for optimal stable positioning
- · Smart recording and playback functions for best recording results



Highlights

Three high-fidelity microphones



Several key components are needed to record sound as naturally as possible in studio-like audio quality: high signal-to-noise ratio, highly dynamic microphones to capture soft tones as well as loud drums, a high-quality microphone suspension to avoid pickup of grip noise, a strong left and right channel separation for human ear live-like effect.

MP3 and PCM recording



Capture your recordings in stereo MP3 and PCM format. The popular MP3 file format allows you to play back your files virtually anywhere and simply share them with others. The PCM (WAV) format allows stereo recording of lossless, uncompressed sound in CD-like audio quality.

8 GB internal memory



Capture and store up to 88 days of continuous recording thanks to the 8 GB of internal memory. A microSD memory card slot for up to 32 GB of additional memory guarantees virtually unlimited recording capacity.

Extra long battery life



The high-capacity Li-ion polymer battery can be easily charged through a standard USB C jack. This guarantees extended battery life for extra-long recording up to 36 hours, ensuring that your recorder will always be ready to work when you are.

Remote control



Control your audio recorder using your smartphone, even from a distance. The Philips VoiceTracer app makes recording events such as lectures much easier and more convenient. You can place your recorder in the front of the room near the speaker, take a seat at the back, and still control recording comfortably and without interrupting the lecture. The Philips VoiceTracer app can be downloaded for free from the Apple App Store or Google Play Store.

Easy sharing



Transfer your recordings straight from your Philips VoiceTracer to your smartphone via Wi-Fi and instantly share them with friends and family using the convenient Philips VoiceTracer app. No need to attach the recorder to your PC using a cable anymore to transfer and share files

Large color display



The large color display offers sharp images, making it easier to see and read everything at first glance. The clear user interface supports seven languages and is optimized for easy, intuitive operation.

Audio scenes



The Philips VoiceTracer comes with preset scenes which automatically adjust the recorder's audio settings depending on what you want to record, whether it is notes, audio for speech recognition, interviews, lecutres, music or meetings.

Highlights

Plug and play



The recorder requires no special installation Simply plug your recorder into your PC or Mac and play back your files or transfer them to your computer right away.

Tripod mount



The integrated tripod thread allows mounting the recorder onto a tripod or camera to capture even clearer sound in an optimal and stable position.

Smart functions



Smart recording functions make it even easier to achieve stunning audio results. The pre-recording and timer functions make sure you don't miss a single bit. Voice-activated recording is a convenient feature for handsfree recording which pauses recording when you stop speaking and resumes automatically when you begin speaking again. Recordings can be edited by overwriting a part or adding a new recording at the end. Long recordings can be split automatically or manually into separate files for easier editing or sharing. Smart playback functions, such as bookmarks and filters, also make it easier and quicker to find the recording you are looking for.

Specifications

Connectivity

Headphones: 3.5 mm, impedance 16 Ohm or

more

Microphone: 3.5 mm, stereo socket,

impedance 2 kOhm

USB: type C, high-speed USB 2.0

Wireless connectivity

Free remote control and sharing app Supported operating systems: Android

12/11/10/9/8, iOS 15/14

Wi-Fi communication mode: personal/mobile hotspot on smartphone (tethering)

Wi-Fi standard: IEEE 802.11 b/g/n/e/i (2.4 GHz

Wi-Fi security: WPA/WPA2-PSK, WPS

Display

Type: LCD color display

Backlight

Diagonal screen size: 2 in/5 cm Resolution: 240 × 320 pixels

Audio recording

Built-in microphone: 2 omni-directional microphones for stereo recording, 1 directionalmicrophone for distance zoom recording

Recording formats: MPEG1 layer 3 (MP3), PCM (WAV)

Recording quality: MP3 (8, 32, 64, 96, 128, 192, 256, 320 kbps), PCM (22 kHz/16 bit, 44.1 kHz/16 bit, 48 kHz/16 bit, 96 kHz/24 bit) Audio scenes: Note, Speech recognition, Interview, Lecture, Meeting, Music, Custom Recording time (built-in memory): 2147 h (MP3, 8 kbps), 536 h (MP3, 32 kbps), 268 h (MP3, 64 kbps), 178 h (MP3, 96 kbps), 134 h (MP3, 128 kbps), 89 h (MP3, 192 kbps), 67 h (MP3, 256 kbps), 53 h (MP3, 320 kbps), 24 h (PCM, 22 kHz/16 bit), 12 h (PCM, 44.1 kHz/16 bit), 11 h (PCM, 48 kHz/16 bit) Pre-recording mode: 5, 10, 15 seconds buffer File editing function: overwrite, append

Bookmark function: up to 32 per file Voice-activated recording: 25 levels Instant one-touch recording Record monitor function

Auto-divide function: 15, 30, 60 minutes

Auto-bookmark function: 5, 10, 15, 30, 60

Recording timer

Wind filter

Limiter (attack time/decay time): slow (32/128 ms), medium (16/64 ms), fast (8/16 ms)
Noise cut

Speaker

Speaker output power: 200 mW Speaker size: 11 × 15 mm

Frequency response: 50-20,000 Hz

Storage media

Built-in memory capacity: 8 GB Built-in memory type: NAND Flash Mass storage class compliant MicroSD card socket: up to 32 GB

Music playback

Sound enhancement: ClearVoice Equalizer: Classic, Jazz, Pop, Rock Playback mode: Repeat file, Repeat all,

Random ID3 tag support Variable playback speed

Supported file formats: MP3, WMA

Convenience

Metallic tripod thread Firmware upgradeable Keypad lock

Multi language: English, French, German, Spanish, Italian, Russian, Polish Variable playback speed

Power

Battery type: built-in rechargeable Li-ion polymer battery Battery capacity: 1000 mAh Battery lifetime: up to 36 hours of recording (MP3, 8 kbps) Rechargeable: yes Charging time (full charge): 3 hours

System requirements

Free USB port

Operating system: Windows 10/8/7, macOS, Linux

Design and finishing

Colour(s): silver/chrome

© 2022 Speech Processing Solutions GmbH.

All rights reserved.

Specifications are subject to change without notice. Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. and are used under license. All trademarks are the property of their respective owners.



Green specifications

Lead-free soldered product

Package contents

Recorder Quick start guide

USB-C cable

Product dimensions

Product dimensions (W \times H \times D): 4.7 \times 12.9 \times 1.9 cm / 1.8 \times 5.1 \times 0.8 in

Weight: 93 g/ 3.3 oz. GTIN-13: 0855971006472

Issue date 2022-01-14

Version 1.0

www.philips.com/dictation