PHILIPS

VoiceTracer

Audio Recorder

Optimized for music 3 high-fidelity microphones XLR adapter cable

8 GB



DVT6510



Superior music recording

in CD-like audio quality

Capture music in outstanding definition and stunning clarity with three high-quality microphones. The remote control enables convenient operation, even from a distance. HighFidelity music recording at it's best.

Superior audio quality

- 3Mic HighFidelity for best-in-class music recording
- \cdot Motion sensor for automatic microphone sensitivity adjustment
- Pre-recording function for never missing a single word
- MP3 recording for clear playback and easy file sharing

Easy and intuitive experience

- Large color display for clear recording status information
- Wireless remote control included for convenient recording
- Rechargeable li-polymer battery for extra-long recording
- Plug and play in Windows, macOS and Linux

Designed around you

- 8 GB memory built-in for up to 88 days of recording
- MicroSD memory card slot for virtually unlimited recording
- $\cdot\;$ Robust and ergonomic metal design for extra durability
- $\cdot\;\;$ XLR adapter cable for easy recording from external sound sources



No 1 in SPS global customer satisfaction survey 09/2017.

3Mic HighFidelity recording



Several key components are needed to record music as naturally as possible in CDlike audio quality: high signal-to-noise ratio, highly dynamic microphones to capture soft tones as well as loud drums, a high-quality microphone suspension to avoid pickup of grip noise, a strong left and right channel separation for human ear live-like effect.

Motion sensor



The built-in motion sensor detects the recorder when it is placed on a desk or held and selects the microphone sensitivity to suit the recording situation preventing you from accidently blocking the audio you want to record.

Pre-recording function



The pre-recording function allows you to record the last five seconds before you press the record key. The device switches into a standby mode and records a five-second loop without saving it. Press the record key to save the five-second loop. This feature allows you to spontaneously record important parts of a conversation.

MP3 recording



Capture your recordings in MP3. The popular file format allows you to play back your files virtually anywhere and simply share them with others.

Large color display



The large color display offers sharp images, making it easier to see and read everything at first glance. The clear user interface supports eight languages and is optimized for easy, intuitive operation.

Wireless remote control



The included remote control enables convenient placement of the recorder to best meet the needs of the audio environment while maintaining ease of operation. Start, pause, and stop recording, without having to clumsily reach over things even from a distance.

Extra long battery life



The high-capacity Li-polymer battery can be easily charged through a standard micro USB jack. This guarantees extended battery life for extra-long recording ensuring that your recorder will always be ready to work when you are.

Plug and play



Thanks to Plug and Play in Windows, macOS and Linux, you can quickly access your recordings without installing any additional software. The recorder is automatically displayed as a removable drive once connected to your computer via USB. It can also be used as a convenient way to store, back up and share files.

8 GB internal memory



Capture and store up to 88 days of continuous recording thanks to the 8 GB of internal memory. VoiceTracer Audio Recorder

Highlights

MicroSD memory card slot



Virtually unlimited recording and storage capacity thanks to a microSD memory card slot supporting up to 32 GB of additional memory.

Robust metal design



Its robust and lightweight design maximizes comfort and the metal surface creates a robust shell around the device. With the integrated fold-out stand you can conveniently position the recorder towards the sound source. Two ergonomically placed soft keys allow for convenient, quick and direct access to the most important functions.

XLR adapter cable



The XLR adapter cable allows you to directly connect your instruments to the recorder for an even crisper and more accurate recording. This is perfect for recording electric guitars or keyboards for instance.

Connectivity

Headphones: 3.5 mm Microphone: 3.5 mm, stereo, without phantom power supply XLR adapter cable: XLR female to 3.5 mm male (an additional phantom power supply might be required for recording with an external microphone) MicroSD card socket USB: high-speed USB 2.0

Display

Type: LCD color display Backlight Diagonal screen size: 1.77"/4.5 cm Resolution: 128 × 160 pixels

Audio recording

Built-in microphone: 3 Mic System, highsensitivity, HQ Stereo, low-noise microphone Recording formats: MPEG1 layer 3 (MP3), PCM (WAV)

Recording modes: PCM 1411 kbps, SHQ 192 kbps, HQ 96 kbps, SP 64 kbps, LP 8 kbps Sample rate: 44,1 kHz (PCM/SHQ), 32 kHz (HQ), 22 kHz (SP), 16 kHz (LP) Bit rate: 8, 64, 96, 192, 1411 kbps File overwrite and append mode Record monitor function Recording time: 2280 h (LP), 284 h (SP), 190 h (HQ), 90 h (SHQ), 12 h (PCM) Silent recording mode

Pre-recording mode

Sound

Sound enhancement: ClearVoice Frequency response: 50–20,000 Hz Signal-to-noise ratio: > 60 dB Speaker output power: 110 mW Speaker diameter: 28 mm

Storage media

Built-in memory capacity: 8 GB Built-in memory type: NAND Flash Mass storage class compliant

Tuner

Frequency range: 87.5–108 MHz Station presets: 20 Auto digital tuning Tuner bands: FM stereo

Music playback

Compression format: MP3, WMA Equalizer settings: Jazz, Pop, Classic ID3 tag support MP3 bit rates: 8–320 kbps WMA bit rates: 48–320 kbps (44 kHz), 64–192 (48 kHz), stereo

Convenience

Firmware upgradeable Keypad lock Multi language: English, French, German, Spanish, Italian, Russian, Polish, Simplified Chinese Variable playback speed Voice volume indicator Voice-activated recording AutoAdjust+ recording AutoAdjust+ recording AutoZoom+ recording: 15 m zoom Calendar search Instant one-touch recording Optimized for notes, conversations, lectures and interviews, meetings

Power

Li-polymer built-in battery Battery lifetime: up to 50/25 hours in LP record mode (built-in memory / microSD memory card)

System requirements

Free USB port Operating system: Windows 10/8/7, macOS 10, Linux

Design and finishing

Colour(s): Champagne/silver shadow

Green specifications

Lead-free soldered product

Package contents

Recorder Remote control XLR adapter cable Carry case USB cable Quick start guide

Product dimensions

Product dimensions (W × H × D): $4.5 \times 12.5 \times 1.8$ cm / $1.75 \times 4.9 \times 0.71$ inch Weight: 85 g/3.0 oz.

© 2018 Speech Processing Solutions GmbH. All rights reserved.

Specifications are subject to change without notice. Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. and are used under license. All trademarks are the property of their respective owners.



Issue date 2018-03-09

Version 1.0

www.philips.com/dictation