

Working smarter together

with dictation solutions from Philips

A dictation and transcription set that combines all the benefits of professional dictation and transcription. The Pocket Memo 488 is an easy-to use dictation recorder that is packed with advanced features. It partners with the desktop transcription system 720 – a dedicated transcription machine that makes a heavy workload manageable. Together, they allow you to produce documents with ease.

Professional recording solution

- · Sensitivity switch for conference or close-range recording
- Automatic gain control for adjustment to optimum recording level
- · End-of-letter index tone for easy file access
- ${\boldsymbol{\cdot}}$ Professional editing via slide-switch operation
- $\boldsymbol{\cdot}$ $\,$ Turbo wind for fast access to any part of the tape
- ${\boldsymbol{\cdot}}{}$ ${\sf Visual}$ indication with LED for showing record status and low battery
- · Voice-activation function for hands-free recording

Professional transcription solution

- · Search forward and skip functions for quick access to the start of the next recording
- · Ergonomic foot pedal for convenient playback control
- · Lightweight stereo headphones for enhanced wearing comfort
- · Tone, speed and volume controls for crystal clear playback at all times
- · Auto backspace pauses transcription without missing a word
- · Turbo wind for fast access to any part of the tape



Highlights

Sensitivity switch

Innovative sensitivity switch for close-range and conference recording with optimal sound quality.

Automatic gain control

The automatic gain control lets you adjust to the optimum recording level at any time.

Audible feedback

The warning tones for end-of-tape and low battery status ensure that no dictation is cut off. The end-of-letter index tone indicates the start of each document and number of recordings.

Professional editing

Easy and quick file editing via convenient slide-switch operation. It offers a fast response and is designed for single-handed operation.

Fast access

The turbo wind function allows very fast and simple access to any part of your tape.

LED indication

The status LED always shows if your battery is running low and the record status.

Voice-activation

Voice-activated recording is a convenience feature for hands-free recording. When enabled, recording will start automatically when you start speaking. Recording stops automatically after you stop speaking and restarts automatically when you start speaking again.

Search functions

Search forward and skip functions allow quick access to the start of the next recording, making it easier to navigate through your recordings. Auto rewind allows you to save time by quickly returning to the beginning of the tape automatically.

Ergonomic foot pedal

Slim, ergonomic design guarantees handsfree control of all playback functions with minimal physical strain.

Lightweight stereo headphones

Lightweight under-the-chin style stereo headphones designed to deliver excellent sound quality, with soft ear cushions for enhanced wearing comfort.

Volume, tone and speed controls

Variable tone, speed and volume controls guarantee crystal clear playback and provide all the necessary features for transcription accuracy.

Auto backspace

The auto backspace automatically replays the last few seconds to review recorded material for transcribing confirmation and accurate and fast transcription.

Turbo wind

The turbo wind function allows you to jump to any part of the tape within seconds and save you valuable time.

Specifications

Pocket Memo dictation recorder

Headphone socket: 2.5 mm Microphone socket: 2.5 mm

Acoustic frequency response: 400-4,000 Hz

Output power: > 100 mW

Product dimensions (W \times D \times H): 128 mm \times

63 mm × 25 mm/ 5.0" × 2.5" × 1.0" Weight: 120 g/ 4.2 oz. (without batteries)

Desktop transcription machine

Headphone socket: 3.5 mm
Foot pedal socket: 3.5 mm
Power supply socket: 12 V DC
Frequency: 200–6.000 Hz
Output power: > 600 mW

Product dimensions: 135 mm × 232 mm ×

50 mm/ 5.3" × 9.1" × 2.0" Weight: 1150 g/ 39 oz

Headphones

Acoustic system: open Magnet type: neodymium

Sound quality: optimized for voice

reproduction
Impedance: 64 Ohm

Maximum power input: 2 × 10 mW

Sensitivity: 103 dB Speaker diameter: 14 mm System: dual sound system Cable connection: one-sided Cable length: 3 m/ 10 ft

Connector: 3.5 mm stereo, right angled

Connector finish: gold-plated

Product dimensions (W \times D \times H): 226 mm \times

130 mm × 25 mm/ 9" × 5" × 1" Weight: 100 g/ 3.5 oz

Green specifications

Compliant to 2011/65/EU (RoHS) Lead-free soldered product

Package contents

Pocket Memo dictation recorder LFH0488 Transcription machine LFH0720 5 × 30 minute mini cassettes LFH0005

Foot pedal LFH2210

Transcription headphones LFH0234

Power supply ACC0155 2 × AA batteries Wrist strap

Accessories

Philips telephone pickup microphone LFH9162

Philips meeting microphone LFH9172 Philips clip-on microphone LFH9173

Philips rechargeable batteries LFH0153

Philips power supply LFH0142

