PHILIPS

PocketMemo

Voice recorder

For Philips mini cassettes

Sensitivity switch

Automatic gain control

Voice-activation function

LFH0488



Simply working smarter

with Philips dictation solutions

Mobility and flexibility are critical in today's fast-moving business environments. The Philips PocketMemo voice recorder gives you the freedom to work when and where you need to.

Superior audio quality

- Sensitivity switch for conference or close-range recording
- Automatic gain control for adjustment to optimum recording level

Enhance your productivity

- End-of-letter index tone for indicating the start of each document and number of recordings
- Professional editing via slide-switch operation
- Turbo wind for fast access to any part of the tape
- Visual indication with LED for showing record status and low battery

Designed for professionals

- · Audible end-of-tape and low battery warning tones for safe recording
- Voice-activation function for hands-free recording
- Transport lock for avoiding unintentional operation
- Internal recharge of batteries for environment friendly use



Highlights

Sensitivity switch

Innovative sensitivity switch for close-range and conference recording with optimal sound quality.

Automatic gain control

The automatic gain control lets you adjust to the optimum recording level at any time.

End-of-letter tone

The end-of-letter index tone indicates the start of each document and number of recordings.

Professional editing

Easy and quick file editing via convenient slide-switch operation. It offers a fast response and is designed for single-handed operation.

Fast access

The turbo wind function allows very fast and simple access to any part of your tape.

LED indication

The status LED always shows if your battery is running low and the record status.

Warning tones

The warning tones for end-of-tape and low battery status ensure that no dictation is cut off.

Voice-activation

Voice-activated recording is a convenience feature for hands-free recording. When enabled, recording will start automatically when you start speaking. Recording stops automatically after you stop speaking and restarts automatically when you start speaking again.

© 2017 Speech Processing Solutions GmbH. All rights reserved.

Specifications are subject to change without notice. Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. and are used by Speech Processing Solutions GmbH under license from Koninklijke Philips N.V. All trademarks are the property of their respective owners.

Transport lock

With the transport lock activated, your voice recorder is protected from unintentional operation.

Internal recharge

Help protect the environment and save your money by simply recharging the batteries of your device instead of buying new batteries (optional Philips rechargeable batteries LFH0153 required).

LFH0488

Specifications

Connectivity

Headphones: 2.5 mm Microphone: 2.5 mm

Sound

Acoustic frequency response: 400–5,000 Hz Output power: > 220 mW

Package contents

PocketMemo voice recorder 2 × AA batteries Luxury pouch Wrist strap

Specifications

Product dimensions (W × D × H): 128 mm × 64 mm × 25 mm/5.0" × 2.5" × 1.0" Weight: 120 g/4.2 oz. (without batteries)

Accessories

Telephone pickup microphone LFH9162 Meeting microphone LFH9172 Clip-on microphone LFH9173 Rechargeable batteries LFH0153 Power supply LFH0142



Issue date 2017-04-10 Version 1.0

www.philips.com/dictation

