

Slide-switch operation





LFH9380

Get more done in less time

with digital dictation

You grew fond of your tape-based recorder but want to increase efficiency? This is where the Pocket Memo 9380 comes into play. With the professional slide switch you can hold on to your working habits and enhance your dictation workflow.

Superior audio quality

- High recording quality in DSS format
- High-quality built-in microphone for excellent sound quality

Enhance your productivity

- SpeechExec workflow software for easy data management
- Professional editing via slide-switch operation
- Priority setting for getting urgent jobs processed first
- Automatic file download via USB for quick transcription

Designed for professionals

- Exchangeable memory card for unlimited recording
- Lightweight metal body for convenient working
- Direct charging via USB for economical recording
- · Voice-activation function for hands-free recording



LFH9380

Highlights

Exchangeable memory card



Virtually unlimited recording capacity thanks to an exchangeable memory card.

Automatic download via USB



When plugged in, the Pocket Memo dictation recorder automatically downloads your audio files directly onto the computer.

High recording quality in DSS



The DSS format was developed for the use in digital voice recorders, achieving a high compression ratio with little loss of quality. The DSS format also allows you to store additional information in the file header, which facilitates the organization and the transcription of dictation files.

High-quality microphone



The high-quality microphone delivers increased recording sensitivity and excellent sound quality.

Lightweight metal body



The ergonomically shaped lightweight metal body is ideal for convenient working over longer periods of time.

Priority setting



With the included priority setting option, urgent recordings get processed first.

Professional editing functions



Easy and fast file editing (insert, overwrite, append) via convenient slide switch.

SpeechExec workflow software



SpeechExec sends your recordings to your assistant for transcription and allows you to monitor the status of your work.

Direct charging via USB



Help protect the environment by simply recharging the batteries of your device using USB instead of buying new batteries.



Philips Pocket Memo digital dictation recorder with SpeechExec workflow software

Specifications

Connectivity

- Headphones: 3.5 mm
- · Microphone: 3.5 mm
- USB: High-speed USB 2.0
- Docking connector • Memory card slot

Display

- Type: LCD
- Diagonal screen size: 44 mm/1.71"
- Resolution: 128 × 128 pixels
- · Backlight: white

Storage media

- · Exchangeable memory card • Memory card types: Secure Digital (SD), Secure
- Digital (SDHC)
- Mass storage class compliant

Audio recording

- Recording formats: Digital speech standard (DSS)
- Built-in microphone: mono
- Recording modes: QP (DSS/mono), SP (DSS/ mono)
- Bit rate: 13.5 kbps (SP), 27 kbps (QP)
 Recording time (2 GB card): 349 hours (SP), 170
- hours (QP) Sample rate: 16 kHz (QP), 12 kHz (SP)

Sound

- · Speaker type: built-in round dynamic speaker
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Frequency response: 300-7,000 Hz (QP), 300-5,700 Hz (SP) Hz

Convenience

- Professional editing functions
- Multiple language support: 4 languages (EN, FR, DE, ES)
- 2 smart buttons
- Author ID setting
- · Control via slide switch
- File lock
- One-thumb operation
- Priority setting
- Voice-activated recording
- Automatic software updates

Power

- Battery type: AAA/LR03 Alkaline, Philips AAA Ni-MH LFH9154
- Number of batteries: 2
- Rechargeable: yes, via USB
- Battery lifetime: up to 23 hours in SP recording mode
- Batteries included

System requirements

- Processor: Pentium IV 1GHz recommended
- RAM memory: 1 GB (2 GB recommended)
- Hard disk space: 100 MB for SpeechExec, 850 MB for Microsoft .NET Framework (Windows)
- Headphone output or speakers
- Operating system: Windows 8/7/Vista (32/64 bit), Mac OS X 10.8/10.7
- Free USB port
- DVD-ROM drive
- Graphics card: DirectX-compliant graphics card with hardware acceleration recommended · Sound device: Windows-compatible sound device

Green specifications

• Compliant to 2002/95/EC (RoHS) · Lead-free soldered product

Accessories

- SpeechExec Dictate software
- USB cable
- Secure Digital memory card
- · Pouch
- Quick start guide
- 2Rechargeable AAA batteries LFH9154

Design and finishing

- Color(s): silver/black
- Material: full metal body

Versions

LFH9380

4-position slide switch (record, stop, play, fast rewind)



• LFH9380/27 with SpeechExec workflow software

Configurable 4-position slide switch (fast forward, play/record, stop, fast rewind)



• LFH9380/01 with SpeechExec workflow software



Issue date 2013-07-26 Version 2.1

© 2013 Speech Processing Solutions GmbH. All rights reserved.

Specifications are subject to change without notice. Philips and the Philips' shield emblem are registered trademarks of Koninklijke Philips N.V. and are used by Speech Processing Solutions GmbH under license from Koninklijke Philips N.V. All trademarks are the property of their respective owners.

www.philips.com/dictation