



PHILIPS

Dictation

Professional
dictation solutions



No 1 in SPS global
customer satisfaction
survey 09/2015.

Taking dictation

to the next level

We believe in the power of simplicity. Our solutions are developed to improve your daily life by making your dictation workflow run as smooth as possible. Our outstanding reputation for quality and reliability has made us the global number one in the professional dictation market. We are the only full solution provider for all your speech-to-text needs, from hardware to software and services.



Dr. Thomas Brauner,
CEO of Speech Processing Solutions



Welcome to the world of

Philips Dictation

Mobile dictation



SpeechAir
Smart voice recorder

6



PocketMemo
Voice recorder

10

Stationary dictation



SpeechMike Premium
Dictation microphone

14



SpeechMike Premium Touch
Dictation microphone

19



SpeechMike
Dictation microphone

20



SpeechMike Air
Wireless dictation microphone

21

Software and solutions



SpeechLive
Cloud dictation solution

24



SpeechExec Pro
Dictation and transcription software

26



SpeechExec Pro
Dictation and speech recognition software

27



SpeechExec Enterprise
Dictation software

28



Remote device management
Central configuration and management software

30

Accessories



Enhance your solution
Transcription and accessories

32



Touch the future of dictation
SpeechAir

SpeechAir

Smart voice recorder

The SpeechAir smart voice recorder saves you time and resources by allowing you to work more flexibly than ever before. Be mobile and take advantage of spare time spent on the go in taxis and airport terminals. Every minute counts.

Product highlights



Three professional microphones
Ultimate sound quality in any recording situation: The 360° microphone is ideal for recording dictations and meetings. The direction microphone is best suited for noisy environments. For VoIP telephony the SpeechAir uses a dedicated microphone.



Dictation workflow
The device comes with an included dictation workflow software*. A cloud-based solution including transcription and speech recognition services is also available on www.speechlive.com for on the go use.



Gorilla glass and antimicrobial housing
Gorilla glass makes the device scratch and shock resistant. The device is shockproof according to military standard. The housing is made of antimicrobial synthetics which work against bacteria and various microorganisms, to ensure hygienic working.



Wear-free slide switch
The ergonomic and wear-free slide switch is designed for efficient single-handed operation. It allows for quick and easy dictation handling (play, pause, stop, fast forward, fast rewind). A customizable function key above the slider gives quick access to the dictation app.



Wi-Fi, LAN, USB and Bluetooth
Save time by transferring your finished recordings wirelessly to your transcription staff and directly access patient or client data. Use Wi-Fi for VoIP calls and access your emails and calendar. Use Bluetooth to send and receive data or to connect external speakers.



Docking station
The included docking station with an anti-theft system automatically transfers all your recordings to your computer and quickly re-charges your device. The LAN connection allows you to transfer your files directly from the docking station without a computer.



Remote administration
Optional remote administration using Philips Remote Device Management software allows IT administrators to manage, configure and update dictation hardware centrally, saving valuable time and resources.



Maximum data security
Recordings are encrypted in real time using the Advanced Encryption Standard (AES) 256bit. A PIN code protects the device against unauthorized use. Settings can be locked, for instance connection to Wi-Fi networks can be restricted.



Android operating system
Android is a secure and intuitive operating system which allows you to install apps on your SpeechAir and have all important applications on one single device.



Barcode scanner and camera
The integrated recorder app comes with professional dictation features such as editing modes, priority, EOL flag, enhanced data and dictation list as well as sending options (to network folder, Philips SpeechLive services or email recipients).



Available versions

- PSP1100 Smart voice recorder
- PSP1200 Smart voice recorder, SpeechExec Pro dictation software
- PSE1200 Smart voice recorder, SpeechExec Pro dictation software with professional speech recognition included

Package contents

- | | |
|--------------------------------|--|
| SpeechAir smart voice recorder | Power supply with international adapters: US, UK, Europe, Asia Pacific |
| Docking station | SpeechExec Pro dictation software (PSP1200) |
| In-ear headphones | SpeechExec Pro dictation and speech recognition software (PSE1200) |
| 2 USB cables | Philips SpeechAir management software |
| User manual | Quick start guide |



* PSP1200



Professional dictation on the go

Pocket Memo

Pocket Memo

Voice recorder

The Philips Pocket Memo digital recorder sets new standards in advanced functionality and style. The ergonomically shaped light-weight metal body is ideal for working over longer periods of time, and the intuitive one-thumb operation offers unparalleled user-friendliness. Coupled with a docking station for uploading your files, going from your voice to your text document has never been quicker.

Product highlights



3D Mic system for best audio quality
Omnidirectional microphone offering 360 degree sound pick-up, ideal for the recording of multiple sound sources such as meetings, and a unidirectional microphone optimized for voice recording and accurate speech-recognition results.*



Integrated barcode scanner
The integrated barcode scanner** enables you to link client or patient data to a recording by simply scanning over a barcode, even from a monitor. This ensures reliable assignment of client or patient IDs and speeds up your workflow.



Wear-free slide switch
The quick-response and ergonomic slide switch is designed for singlehanded operation of all recording and playback functions, allowing easy and quick file editing (insert, overwrite, append). It operates with an optical sensor, making it wear-free and durable.



Large, high-resolution color display
The large full-color display offers sharp images, making it easier to see everything at first glance. The clear user interface is optimized for easy, intuitive operation.



Motion sensor
The motion sensor selects the appropriate microphone in every situation and increases battery life by automatically switching into standby mode whenever the device is idle.



High data security
Recordings are encrypted in real time using the Advanced Encryption Standard (AES) 256bit. The device itself can be assigned a PIN code to protect against unauthorized use or file playback.*



Extended battery runtime
In addition to the motion sensor, the light sensor also adjusts the brightness of the display and helps save battery life. The removable high capacity Li-ion battery can easily be charged via USB.



Philips Remote Device Manager
Allows IT administrators to centrally manage, configure and update dictation hardware from Philips, saving valuable time and resources. Managing device settings for individuals, groups and teams or the whole organization is easily done remotely.*



Classic mode
Many users still love their analog devices for their simplicity and userfriendliness. The optional classic mode gives the user the look and feel of working with an analog device while retaining the advantages of digital technology and keep focused on the essentials.



Docking station
The stable docking station provides speedy charging and automatic transfer of your recordings. With an optional foot control, the docking station enables hands-free recording and transcription.



Available versions

- DPM8100** Slide-switch style: (record, stop, play, fast rewind)
- DPM8000** Slide-switch style: (record, stop, play, fast rewind), SpeechExec Pro dictation software
- PSE8000** Slide-switch style: (record, stop, play, fast rewind), SpeechExec Pro dictation software with professional speech recognition included
- DPM8200** Slide-switch style: (fast forward, record/play, stop, fast rewind), SpeechExec Pro dictation software
- PSE8200** Slide-switch style: (fast forward, record/play, stop, fast rewind), SpeechExec Pro dictation software with professional speech recognition included
- DPM8300** Slide-switch style: (fast forward, record/play, stop, fast rewind)
- DPM8500** Slide-switch style: (record, stop, play, fast rewind), integrated barcode scanner

Package contents

- | | |
|---|--|
| Pocket Memo digital voice recorder | SpeechExec Pro dictation software (DPM8000 and 8200) |
| Docking station (DPM8000 series) | SpeechExec Pro dictation and speech recognition software (PSE8000 and 8200) |
| Rechargeable battery | Memory card |
| USB cable | Pouch |
| User manual | |



* DPM8000 series
** DPM8500



Best-in-class recording

SpeechMike

SpeechMike Premium

Dictation microphone

The SpeechMike Premium offers a precision microphone for studio recording quality and outstanding speech recognition results. It also features the world's first motion sensor in a stationary dictation device.

Product highlights



De-coupled microphone

The microphone is decoupled from the device's housing, which guarantees that almost no background, touch, click, air or structure-borne noise is recorded. This technique is derived from studio microphones to guarantee outstanding speech recognition results.



Integrated barcode scanner

The SpeechMike Premium is also available with an integrated barcode scanner to link client or patient data to a recorded file simply by scanning a barcode.



Integrated pop filter

Fleece inserted above and below the microphone capsule filters out sound distortions such as pop and hiss noise, guaranteeing perfect results even if dictating closely into the microphone.



Ergonomically shaped

The device is designed to fit perfectly into the hand and reduce unintentional pressing of buttons. The trigger and the 'command' button on the back of the device are engineered to be in easy reach for the fingers.



Large speaker area

The SpeechMike Premium is equipped with an extra-large speaker, enabling it to not only record but also play back recordings in clear and crisp quality.



Metal microphone grille

The metal grille comes with specially designed hexagonal openings which allow three times more sound to reach the microphone than its predecessor, engineered to provide crystal clear recordings.



Integrated motion sensor

The integrated motion sensor detects when the device is idle and placed on the table. It automatically mutes the microphone until it is picked up again.



Polished, antimicrobial housing

The housing and the buttons of the SpeechMike Premium are made of antimicrobial synthetics that work against a wide range of different microorganisms. The polished, high quality pearl metal surface also makes the device non-sensitive to touch noises and fingerprints.



Wear-free slide switch and push button

The SpeechMike Premium comes with a slide-switch or a push-button operation. The slide switch is wear-free and ergonomically shaped with a softly ribbed surface for smooth tactile feedback and comfortable and intuitive utilization.



Freely configurable keys

The SpeechMike Premium has freely configurable keys which are especially useful for programming speech recognition commands. The device can be personalized for any user and application.



Mouse function

The device comes with a touch sensor or trackball. This allows the user to easily control and navigate within applications while recording, without having to switch between the mouse and microphone.



Highly compatible

Customers can upgrade from their previous SpeechMike model without installing additional software. For integrators, this means no changes need to be implemented and the existing SDK can be used.



Available versions

- LFH3500 Push-button operation
- LFH3510 Slide-switch style (record, stop, play, fast rewind)
- LFH3520 Slide-switch style (fast forward, record/play, stop, fast rewind)
- LFH3530 Push-button operation, limited white edition
- SMP3700 Push-button operation, touch sensor
- PSE3700 Push-button operation, touch sensor, SpeechExec Pro dictation software with professional speech recognition included
- SMP3710 Slide-switch style (record, stop, play, fast rewind), touch sensor
- SMP3720 Slide-switch style (fast forward, record/play, stop, fast rewind), touch sensor
- SMP3800 Push-button operation, touch sensor, integrated barcode scanner
- SMP3810 Slide-switch style (record, stop, play, fast rewind), touch sensor, integrated barcode scanner



LFH3530

Package contents

- | | |
|---|--|
| SpeechMike Premium dictation microphone | User manual |
| USB cable | SpeechExec Pro dictation and speech recognition software (PSE3700) |
| Microphone holder | Quick start guide |



SMP3720

SpeechMike

Dictation microphone

Unique features such as excellent ergonomics and anti-microbial housing have made the SpeechMike dictation microphone a staple product in medical practices around the world.

Product highlights



Noise-canceling microphone
The advanced microphone design and an optimized frequency response rate cater for the best speech recognition results.



Antimicrobial surface
The antimicrobial surface is important for use in a clinical environment. This feature was achieved by adding a substance to the plastic that impedes the reproduction of microorganisms, thus improving hygiene.



Geared for speech recognition
The SpeechMike features preconfigured buttons for direct control of Dragon NaturallySpeaking, the voice recognition solution from Nuance.



Ready for integration
Philips provides a software development kit (SDK) for speech, office, and business application developers that allows for convenient programming of interfaces when integrating the SpeechMike into professional information and dictation solutions.



Available versions

- LFH3200** Push-button operation
- LFH3210** Slide-switch style (record, stop, play, fast rewind)
- LFH3220** Slide-switch style (fast forward, play/record, stop, fast rewind)

SpeechMike Air

Wireless dictation microphone

Enjoy all the benefits of the SpeechMike dictation microphone without being bound to your desk by a cable.

Product highlights



Wireless dictation
The SpeechMike Air requires no cable. It connects wirelessly to your computer, allowing for more comfortable and flexible working. Your voice data is encrypted and securely transferred to your PC from up to 33 feet (10 meters) away. The dictation microphone has a long lasting battery, which can be quickly charged using the included AirPort docking station.



Ergonomic zone design
Through extensive user tests Philips has managed to come up with a design which offers maximum comfort, even when used extensively over longer periods of time. The device fits comfortably into your hand and the most frequently used buttons are located closest to the thumb and index finger (at the back of the device).



Integrated trackball
The Philips SpeechMike Air offers an integrated trackball that allows the user to easily navigate through documents and files without using a mouse.



Geared for speech recognition
The SpeechMike Air features preconfigured buttons for direct control of Dragon NaturallySpeaking, the voice recognition solution from Nuance.



Available versions

- LFH3000** Push-button operation
- LFH3010** Slide- switch style (record, stop, play, fast rewind)
- LFH3020** Slide-switch style (fast forward, play/record, stop, fast rewind)

Solutions

and software



SpeechLive

Cloud dictation solution



Philips SpeechLive is a cloud-based dictation workflow solution which enables you to manage your dictations from both your office and on the go. Send recordings to your assistant or have them written up by our professional transcriptionists or our speech recognition software.

Product highlights



Constant file access

Access all your dictation files anywhere, anytime. Even without Internet access, you can still work in local mode and synchronize all your dictation files when you are online again.




Backup and restore function

The automatic backup function protects your data against accidental loss. Your dictation files are always safe, even if your computer crashes, you suddenly lose Internet connection or unintentionally erase your data.



Easy set-up and local support

Setting up SpeechLive is quick and easy. The fast and intuitive installation process ensures you are ready to go within minutes. If needed, authorized SpeechLive partners will offer local support and assistance.



Independence from local infrastructure

With SpeechLive you are ready to go – no local server infrastructure is required. Your files are always available independent from changes to your IT environment.



Web browser-based workflow management

The workflow can conveniently be managed from your web browser. No need to install any complicated software. Settings can be readjusted anywhere, anytime.



Flexible subscriptions

SpeechLive offers flexible subscription options. The number of users can be adjusted at any time, making sure the solution always fits your budget.



Maximum file security

SpeechLive offers maximum connection security using the HTTPS protocol, automatic double encryption in real-time, server mirroring and an automatic back up function.



Optional transcription service

If you don't have an assistant available you can send your recordings straight to the Philips SpeechLive transcription service. Our professional transcriptionists will type up your documents and send them back to you within in no time.



Excellent workflow management

Adapt the solution to your company's way of working. Administrators can easily define authors and typists, as well as assigning the workflow from anywhere in the world, to balance workload.



Optional speech recognition service

If you require an urgent transcription, simply dictate your notes or tasks and send them to the Philips SpeechLive speech recognition service. You will receive the finished document immediately.

How it works



01 Record your voice

Record your ideas, tasks and documents wherever you are and send it to SpeechLive. All your recordings are safely stored in the cloud.

02 Select your transcription option

Choose whether you want to send your recordings to your assistant, the Philips SpeechLive speech recognition software or the Philips SpeechLive transcription service.

03 Receive text file

Save time and resources by letting others do the typing for you. You can receive your recordings as finished text files straight to your email.

Be productive on the go

You can professionally record, edit and send dictations for transcription directly from all your devices. SpeechLive works with your Philips voice recorder, as well as your smartphone. The Philips dictation recorder app is free with every SpeechLive subscription and can be used simultaneously with your voice recorder.



**30-day
free trial**
www.speechlive.com

SpeechExec Pro

Dictation and transcription software



SpeechExec Pro dictation and transcription software links authors and transcriptionists. It facilitates communication, individual workflow settings and organizational flexibility to help save time and resources. Authors can record directly into the software using a dictation microphone and transcriptionists can playback and conveniently transcribe these files using a foot control.

Product highlights



Efficient workflow management

Easily monitor and manage the workflow between authors and transcriptionists. Recordings and the resulting written documents are automatically routed to the appropriate person for quicker turnaround times.



Automated download

SpeechExec Pro allows authors and transcriptionists to automatically download all their dictations from their voice recorder straight into the software and route to the appropriate destination via their local network, FTP server, SpeechLive or email.



Worklists and organization

Worklists help both authors and transcriptionists monitor their work statuses. They save time used for unnecessary status update communication between parties. Files can be organized into sub folders, assigned specific properties and comments and marked as urgent to help organize and prioritize tasks.



Geared for speech recognition

Speech recognition software from Dragon can be seamlessly connected with solution. Whether the author is dictating directly into the software using a Philips microphone or uploading recorded files from a voice recorder, they will receive accurate speech recognition results which will help speed up their workflow.



Data security and backup

Real-time file encryption (256 bit) and secure file transfer grant only authorized individuals to access documents. The optional automatic backup function protects data against accidental loss.



Individual sort and filter options

Both author and transcriptionist benefit from individual sort and filter options to find dictations and documents even quicker and always stay highly organized.



Seamless integration into SpeechLive

Philips SpeechLive cloud dictation workflow solution gives users constant file access via browser for greater flexibility and mobility. With SpeechLive, authors can dictate with their smartphone from anywhere and send dictations directly to their SpeechExec software. It also features a transcription service, where trained professionals quickly type up recordings for the author.



SpeechExec transcription player

The software comes with a conveniently integrated transcription player with pause, fast forward and rewind options. Together with the configurable Philips foot control it allows for comfortable and quick transcription. Predefined templates can be used, so documents are automatically created with the appropriate header and footer, saving even more time.



SpeechExec dictation recorder

With the integrated dictation recorder, authors can record directly into their SpeechExec software. The software works perfectly with Philips SpeechMike dictation microphones and allows for quick and easy control of all recording and playback functions such as insert, overwrite and append. Function buttons can be individually programmed for added user convenience.



New task notifications

Transcriptionists can receive alerts whenever new recordings are assigned to them, making sure no important recordings are missed. These notifications appear on their screen in real-time in a discreet popup window.

Available versions

LFH4400 Pro dictation software

LFH4500 Pro transcription software


SpeechExec Pro

Dictation and speech recognition software



SpeechExec Pro is now also available with included professional Dragon NaturallySpeaking speech recognition software (PSE4400 and PSE4500). You can speak naturally into your dictation microphone and see the text appear on your screen immediately. If you are on the go, you can record your voice using a Philips SpeechAir for example, and send it directly to your SpeechExec solution. Your entire file will be transcribed for you automatically by the software.

Additional product highlights



Integrated speech recognition

The integrated Dragon professional speech recognition software allows you to turn speech into text immediately using any Philips dictation recording devices and achieve superb audio quality, high accuracy, and easy hardware administration.



On- and offline speech recognition

The integrated speech recognition software supports both real-time speech recognition with dictation microphones and the transcription of audio files pre-recorded with portable voice recorders.



Load in your own vocabulary

The integrated speech recognition software can learn new words and commands. It also allows users to load in their existing vocabulary lists and previously saved commands, ensuring high speech recognition accuracy is achieved right away.

Benefits

- + Accurate immediate transcription
- + Possibility to create individual user voice profiles
- + You can integrate it into any of your applications and dictate directly into predefined templates
- + No internet connection required, software is located locally on your PC or server
- + Supports creation of individual vocabularies with external tools (such as nsadmin, DDT and vocool)
- + Supports upgrade of Dragon 12/13 Professional user profiles
- + Save time even when your assistant is not available to transcribe recordings for you
- + No need to buy an additional, expensive speech recognition software

Available versions

PSE4400 Pro dictation software with professional speech recognition

PSE4500 Pro transcription software with professional speech recognition

SpeechExec Enterprise

Dictation software



Philips SpeechExec dictation software links authors, typists and administrators, facilitating communication, individual workflow settings, and organizational flexibility. SpeechExec Enterprise offers the full dictation workflow, with many benefits especially for the administrator. Ideal for organisations with many users such as hospitals or legal firms.


Product highlights



Sophisticated automated workflow
Easily monitor and manage the workflow between authors and transcriptionists. Recordings and the resulting written documents are automatically routed to the appropriate person for quicker turnaround times.



Individual sort and filter options
Both author and transcriptionist benefit from individual sort and filter options to find dictations and documents even quicker and always stay highly organized.



Central administration
Increase your organization's productivity by managing users, licenses, and system settings remotely. The central administration function facilitates the configuration of worklist columns, filters, and job information. Active Directory support also allows for easier settings management.



Geared for speech recognition
Speech recognition software such as Dragon NaturallySpeaking can be seamlessly integrated into the solution. Whether you are dictating directly into the software using a Philips microphone or uploading recorded files from a voice recorder, you will receive extremely accurate speech recognition results which will help speed up your workflow.



Remote hardware administration
Remote hardware administration allows you to centrally configure the buttons of Philips' dictation microphones and update the firmware.



SpeechExec transcription player
The software comes with a convenient integrated transcription player with pause, fast forward and rewind options. Together with the configurable Philips foot pedal it allows for comfortable and quick transcription. Predefined templates can be used, so documents are automatically created with the appropriate header and footer, saving you even more time.



Citrix and VMware ready
Support for Citrix and terminal server environments allow on-demand application delivery. SpeechExec can be virtualized, centralized, and managed in the data center and instantly delivered as a service to users anywhere. In addition, SpeechExec is compatible with the HL7 interface. SpeechExec Enterprise can work as a communication interface between the dictation workflow and the hospital information system (HIS).



SpeechExec dictation recorder
With the integrated dictation recorder, authors can record directly into their SpeechExec software. The software works perfectly with Philips SpeechMike dictation microphones and allows for quick and easy control of all recording and playback functions (insert, overwrite and append). Function buttons can be individually programmed for added user convenience.



Highest security
Real-time file encryption (256 bit), password protection and secure file transfer grant only authorized individuals to access documents. The optional automatic backup function protects data against accidental loss.



New task notifications
Transcriptionists can receive alerts whenever new recordings are assigned to them, making sure no important recordings are missed. These notifications appear on their screen in real-time in a discreet popup window.


Included modules



Enterprise Manager
The central administration module for the system defines user settings, job information settings, licenses, and supports Microsoft's Active Directory services.



Enterprise license server
The license server manages licensing for the dictation and transcription modules, the Workflow Manager and the Statistics Module.



Enterprise Dictate for authors
This dictation module processes voice files from digital voice recorders (Philips SpeechAir, Philips Pocket Memo and Philips Dictation apps) and desktop dictation devices (Philips SpeechMike). Recording functions, priority, indexing, work routing and keywords can be customized to the author's needs. Attaching documents to dictation files keeps data organized.



Enterprise Transcribe for transcriptionists
The transcription software allows efficient access to digital voice files. Visual workflow management, including sort, search, and filter options and job information such as author, length and priority, assure productive transcription and fast document turnaround. With the ergonomic Philips foot control all transcription and playback functions can be controlled with your foot keeping your fingers on the keyboard.

Optional modules



Workflow Manager
Set up and automate a workflow for moving, copying and deleting dictation files based on predefined rules and schedules and send automatic email notifications.



Statistics Module
Receive comprehensive statistics on dictation, transcription, job status and workload, including graphics. Results can be exported to Microsoft Excel, Word, Adobe Acrobat, Crystal Reports or displayed as RTF documents.



Remote Device Manager
IT administrators can centrally configure all Philips dictation hardware and programmable accessories like the foot control, saving time and resources.



SpeechExec Mobile Server
Manage dictations from the Philips Dictation Recorder app for iPhone, BlackBerry, Android or Windows and distribute the recorded files automatically in SpeechExec Enterprise.

Available versions

LFH7330 Enterprise dictation workflow solution

Remote device management

Central configuration and management software

The Philips remote device management software allows administrators to centrally configure Philips dictation devices, saving valuable time and resources.

Product highlights



Central configuration of hardware
With the unique Philips remote device manager Philips dictation devices can be conveniently managed centrally and device configurations can be assigned to users, device types, and even individual units.



Remote deployment of settings
All major functions of SpeechAir, PocketMemo, SpeechMike Premium, SpeechMike Air, SpeechMike and foot controls can be centrally configured and then rolled out remotely to any device within the organization. Fully location-independent.




Automatic firmware updates
Easily upload firmware files for SpeechAir, PocketMemo, SpeechMike Premium, SpeechMike Air and SpeechMike. The version of the firmware will be read automatically and stored in the database. After uploading the firmware, it can be assigned to all concerning device configurations in one operation.



Seamless device integration
The Philips remote device management software seamlessly integrates SpeechAir, PocketMemo, SpeechMike Premium, SpeechMike Air, SpeechMike and foot controls for central configuration on an unprecedented scale.




Centrally configurable settings
Administrators can easily manage, update, and maintain the configuration and settings of individual units, groups of units, or all units with the Philips remote device management software. The changes can then be automatically uploaded to assigned devices.



Free version for up to ten devices
A free version of the Philips remote device management software is available via an online download. It supports reliable management and programming of up to ten devices.



Remotely restore settings
Individual user settings of Philips dictation devices can be remotely restored and backed up by administrators anytime and anywhere – in case of loss or unintentional deletion, as well as for new-device setup.



Supports virtual desktop infrastructures
The Philips remote device manager can now also be used with Citrix, Microsoft WTS/RDS and VMware Horizon View environments. Further information can be found in the technical documentation.

Available versions

LFH7470 Remote device management software

	Pro	Pro with integrated speech recognition	Enterprise
Author			
Automated workflow	✖	✖	✖
Attach documents to recording	✖	✖	✖
Record directly into software	✖	✖	✖
Download recordings from voice recorder	✖	✖	✖
Predefined templates	✖	✖	✖
Supports Dragon NaturallySpeaking	✖	✖	✖
Password protected log in			✖
Integrated speech recognition		✖	
Load in your own vocabulary		✖	
Support Philips dictation recorder app	via SpeechLive	via SpeechLive	via Mobile Server

Transcriptionist

Automated workflow	✖	✖	✖
Attach documents to recording	✖	✖	✖
Download recordings from voice recorder	✖	✖	✖
Playback dictations with foot control	✖	✖	✖
Notifications for transcriptionists	✖	✖	✖
Speech recognition connector (to Dragon Nuance)	✖	✖	✖
Predefined templates	✖	✖	✖
Password protected log in			✖

Admin & IT Manager

Automated workflow	✖	✖	✖
Silent setup	✖	✖	✖
SpeechLive option	✖	✖	
Licensing	Web	Web	Local server
Back up function	✖	✖	✖
Encrypted, secure data transfer	✖	✖	✖
Hardware support for all Philips products	✖	✖	✖
Central administration			✖
Remote hardware configuration and administration			✖
Remote desktop: Citrix/WTS/VMware			✖
Active Directory			✖
Sophisticated workflow configuration			✖
Statistical reporting			✖
Interfaces (e.g. HL7 to hospital information systems)			✖



Accessories
and transcription

Enhance your solution

Transcription and accessories

Make the most out of your dictation solutions with our premium accessories.



Transcription-Headphones LFH0334
Lightweight under-the-chin style stereo headphones designed to deliver excellent sound quality, with soft ear cushions for wearing comfort, and a hanging bracket that attaches the headset to a monitor.



Foot pedal ACC2300 series
The ergonomic design has been developed based on detailed research into the movements made during transcription. Transcriptionists can stop and start playback with only a slight movement of their foot tip, without lifting the foot unnecessarily, which increases the user's efficiency.



Transcription set LFH7177
The transcription set is a digital document creation solution specifically designed to make transcription easy and intuitive. It includes a lightweight headset, an ergonomic foot pedal and the standard Philips SpeechExec dictation workflow software.



Professional transcription set LFH7277
The professional transcription set also includes the lightweight headset and the ergonomic foot pedal, but comes with the enhanced SpeechExec Pro dictation workflow software. This offers advanced functionality such as speech recognition integration.




SpeechAir case ACC1120
The SpeechAir case has been developed to ensure maximum protection for your voice recorder, making it perfectly suitable for every working environment. The clip allows you to keep your recorder within reach at all times. Enjoy full protection and mobility.



Pocket Memo Wi-Fi adapter ACC8160
The innovative Philips Wi-Fi adapter instantly sends your files from the dictation recorder to your transcriptionist. Just dock the recorder to upload your dictation files directly to the company network using built-in WiFi. Administrators can easily deploy automatic firmware updates for Pocket Memo voice recorders via an easy Web browser interface.



Pocket Memo docking station ACC8120
The Pocket Memo docking station allows you to easily transfer all your dictations to your computer as well as quickly charge your device, so you are always ready to go. Combined with the optional foot pedal, it is possible to record hands-free and even transcribe without a computer.



360° Meeting microphone LFH9172
The perfect complement for digital conference recording systems. The Philips meeting microphone delivers brilliant sound quality, accompanied by outstanding ease of use. Revolutionary technology in a straightforward form.



SDHC memory card ACC9008
The Philips SD memory card combines massive storage capacity and fast data transfer rates in a memory card no bigger than a postage stamp. It is the ideal expansion option for your Philips Pocket Memo voice recorder.



Li-ion battery ACC8100
With the new rechargeable lithium ion battery for Philips Pocket Memo voice recorders, you can record even longer now. No more buying of disposable batteries is needed. Li-ion batteries can store a large amount of energy in a very small, lightweight package. They are quick-charging, safe and reliable.

Global leader in professional dictation solutions

Philips Dictation is the global leader in professional dictation solutions. Founded in Austria in 1954 we have been a driving force for innovative voice-to-text solutions for over 60 years. The company developed ground-breaking products such as the Philips Pocket Memo

voice recorder, SpeechMike Premium dictation microphone, SpeechExec workflow software, SpeechLive cloud dictation solution and the brand-new SpeechAir smart voice recorder. Philips Dictation combines latest innovation with excellence and superior quality.



© 2017 Speech Processing Solutions GmbH. All rights reserved. Philips and the Philips' shield emblem are registered trademarks of Koninklijke Philips N.V. and are used by Speech Processing Solutions GmbH under license from Koninklijke Philips N.V. All trademarks are the property of their respective owners.



www.philips.com/dictation
www.speechlive.com